


Two-pieces shipping

TSA-16	Lower shell				Upper shell				Solution	
	L1 mm	W1 mm	H1 mm	Weight kg	L2 mm	W2 mm	H2 mm	Weight kg	Weight kg	Bottle
LJ-11	2,680	1,430	1,630	1,900	2,790	1,190	1,040	1,000	600	3
LJ-12	2,680	1,430	1,630	2,000	2,790	1,190	1,040	1,000	600	3
LJ-13	3,700	1,430	1,630	2,400	3,800	1,190	1,040	1,400	800	4
LJ-14	3,700	1,430	1,630	2,500	3,800	1,190	1,040	1,400	800	4
LJ-21	3,780	1,590	1,710	3,100	3,860	1,370	1,110	1,700	900	4
LJ-22	3,780	1,590	1,710	3,200	3,860	1,370	1,110	1,800	1,100	4
LJ-23	4,760	1,590	1,710	3,600	4,920	1,370	1,110	2,200	1,300	5
LJ-24	4,760	1,590	1,710	3,800	4,920	1,370	1,110	2,300	1,400	5
LJ-31	4,920	1,680	1,820	4,700	4,970	1,370	1,120	2,800	1,600	6
LJ-32	4,920	1,680	1,820	4,800	4,970	1,370	1,120	3,000	1,700	6
LJ-41	4,890	1,750	2,010	5,900	5,120	1,530	1,180	3,200	2,000	8
LJ-42	4,890	1,750	2,010	6,000	5,120	1,530	1,180	3,400	2,100	8
LJ-51	5,050	2,040	2,240	7,800	5,260	1,840	1,330	5,200	2,400	9
LJ-52	5,590	2,040	2,240	8,600	5,800	1,840	1,330	5,500	2,700	10
LJ-53	6,090	2,040	2,240	9,200	6,300	1,840	1,330	5,800	3,000	11

- Note) 1) Above dimensions are not included packing size.
 2) Control panel (1600 x 600 x 300mm, 100kg) is shipped separately.
 Control panel of LJ-41,42,51,52 and 53 is shipped with lower shell.
 3) Solution bottle size is 600 x 600 x 950mm.
 The solution weight is included bottle weight.



Carrier
SANYO

**Shipping dimensions
(Two-pieces shipping)**

Model

TSA-16LJ

Drawing code

LJ-008-131-21-1